


No: 20132-110

## APC applicator 240 SC



### Dimensions and weight

Dimensions	Ø 2,3 mm
Length	240 mm

### Basic features

Flexibility	rigid
Beam forms	S = Side Fire Spot Beam
Shape / Forming	S

### Cleaning and Reprocessing

Cleaning in washer disinfectant	max 95 °C
Sterilization in autoclave	max 138 °C

### Standards

Classification acc. to 93/42 EWG	IIb
Protection category acc. to EN 60 601-1	
Type acc. to EN 60 601-1	

### Additional product information

Packaging unit	1 Piece
Max. electrical capacity	4.3 kVp