

No: 20190-067

## Slim-Line electrosurgical pencil with 2 buttons



### Dimensions and weight

Cable length	with connecting cable 4 m
Shaft diameter	2.35 mm

### Basic features

Compatibility	VIO, ICC, ACC, non-ERBE units
Connection	International

### Cleaning and Reprocessing

Cleaning in washer disinfectant	max 95 °C
Sterilization in autoclave	max 138 °C

### Standards

Classification acc. to 93/42 EWG	IIb
Protection category acc. to EN 60 601-1	
Type acc. to EN 60 601-1	

### Additional product information

Packaging unit	1 Piece
Max. electrical capacity	6 kVp